

Tel. +39 02 36569371 info@danetech.it www.danetech.it



## ADT878-TPW-KIT Lotto 1 - Edificio A13-14 20017 Rho (MI) Triple Point of Water Realization Kit



- One touch TPW cell realization
- Extremely affordable intrinsic standard
- Self-calibration feature
- Automatically update reference probe TPW values
- Easily maintain temperature working standards
- Fully self-contained

### **OVERVIEW**

The Additel 878 TPW Kit provides everything you need to utilize our model ADT878-160 Reference Dry Well as an intrinsic standard. The triple point value (0.01°C) is key to ITS-90 temperature probe calibration work. Traditional methods take time and practice to realize the triple point of water. Additel has now simplified this process with an automatic TPW realization feature. Simply insert the cell and PRT into the Reference Dry Well and run the preprogrammed procedure. The automation in the firmware will alert when the cell is super cooled. Remove the cell and give it a shake and now you can maintain the triple point in the reference well. With the help of this easy to use kit, users can quickly and easily realize and maintain our custom fit TPW cell, then record/update those ever critical TPW values for all your PRTs.


01

### Addite

Metrology Made Simple

### **Accuracy Verification Loop**

The triple point of water (TPW) is a critical intrinsic standard and ITS-90 reference point that every owner of a reference PRT or SPRT should have. Using the TPW to check reference temperature probes is the most convenient and affordable way to ensure confidence in your measurements. By regularly checking the drift of your temperature sensor, you can know with certainty if your sensor is in tolerance or not. The International Temperature Scale of 1990 (ITS-90) supports the TPW to be a reliable standard to check your reference PRT. By using the ADT878-160 Reference Dry Well, you can maintain and realize the TPW cell, which in turn can verify your reference PRT. This helps to bring everything full circle, the reference PRT can be used in the self-calibration mode to validate the display accuracy of the





**Accuracy Verification Loop** 

### **SPECIFICATIONS**

Specification	Display	
Uncertainty	<0.0005°C <sup>[1]</sup>	
Immersion depth/ID	115 mm X 8 mm	
External Dimensions	160 mm X 25 mm	
Cell material	Borosilicate Glass	
Realization time	20 mins	
Estimated working time	2 hours	
Recommended thermal Fluid	Ethanol	
Warranty	1 year	

[1] Specification relates to the overall uncertainty when using the shake method of realizing the cell and maintaining it in the ADT878-160. Call for more info.

# 8 mm 25 mm

**TPW Cell Size** 

### **Ordering Information**

### **Model Number**



### Accessories

Included Accessories			
Model	Description	Picture	
1520000292	TPW cell, 1 pc.	Ĭ	
1223000410	Cell basket, 1 pc.		
1223000411	Basket cover, 1 pc.		

Included Accessories			
Model	Description	Picture	
1223000412	Basket cover with hole, 1 pc.	•	
1520000291	Support ring, 1 pc	<b>Q</b>	
1810298212	Cell removal tool, 1 pc		
1520000290	Bottom cushion, 1 pc.	*	

Phone: 714-998-6899 Fax: 714-998-6999 Email: sales@additel.com Rev # 20200916

**Corporate Headquarters** 2900 Saturn Street #B Brea, CA 92821, USA

Salt Lake City Office 1364 West State Rd. Suite 101 Pleasant Grove, UT 84062, USA