

SQ-6

Electro-acoustic coupler



⚙️ Applications

- ✓ pressure chamber secondary calibration
 - microphones (IEC 61094-5)
 - sound level meters and sound level measuring chains (IEC 61672)
- ✓ phase calibration of intensity probes
- ✓ for ½" capsule devices

⚙️ Selected Data

- ✓ high sound pressure level:
 - 114 dB: 10 Hz ... 20 kHz
 - 148 dB: 16 Hz ... 5 kHz
- ✓ low distortion over the entire frequency range: < 0.3 % (THD)

💡 Features

- ✓ innovative, compact design
- ✓ rotary clamp closures ensure precise and efficient alignment and sealing of sensors
- ✓ modular sealing configuration to satisfy individual test specimen requirements
- ✓ fully symmetric electro-acoustic topology ensuring a more uniform sound field for reliable results
- ✓ standard photo thread compatible mounting for various arrangements







Technical Data

Sound field	Pressure chamber
Frequency range	10 Hz...20 kHz
Max. electrical power of sound source	2.4 W
Distortion factor at 94 dB	< 0.3 % (THD)
Devices under test (DUTs)	1/2" microphone capsules
Maximum sound pressure level¹⁾	10 Hz...20 kHz 114 dB
	16 Hz...5 kHz 140 dB...148 dB
Dimensions (H x W x L)	60 mm x 60 mm x 42 mm (2.4 in x 2.4 in x 1.7 in)

All specifications are at room temperature unless otherwise specified. ¹⁾ Depending on frequency range, DUT type and amplifier.

Performance





System Components

- ✓ SQ-6 electro-acoustic coupler
- ✓ standard power amplifier, incl. power supply
- ✓ O-rings and spacers for various 1/2" microphone capsules
- ✓ table tripod with 360° ball head, 3 working heights
- ✓ LS adapter (for WS2P microphones)
- ✓ system cable and transport case



▲ **Application example:** Calibration of a typical measuring microphone using the SQ-6



⊕ Accessories (optional)

- ✓ reference standards (recommended)
- ✓ 1/2" condenser microphone capsule type LS2P or WS2P with amplifier
- ✓ fixture for sound level meters or heavy microphones
- ✓ spacer kit for intensity probes

System integration



The **SQ-6** acoustic coupler from SPEKTRA can be easily integrated into a **CS Q-LEAP™** system solution. With the HERO™ controller, various excitors and a software with extensive functions, we guarantee an efficient workflow for your individual test and calibration tasks.